



Sample photo

Order symbol: PC 125/75 HG
Product nbr: 6011308
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074014023
El. number:
Finland: 3420332
Electric No. Denmark: 8212022276
Electric No. Italy: 7351057
Electric No. Sweden: 6011308

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	130	130	75	MIN 10	DIN-15 Mounting rail
inch:	5.1	5.1	3.0	MIV 10	DIN-35 Mounting rail
Materials:			FP A 125/130	Front plate (Aluminium)	
Material:	Polycarbonate		HFP 130	Front plate hinge series	
Base colour:	RAL 7035 -light grey		FP 22046	Wall fastening lug (4 pcs)	
Cover screws material:	Polyamide		Rating:		
Cover colour:	RAL 7035 -light grey		Ingress Protection (EN 60529): IP66/IP67		
Cover screws colour:	Grey		Impact Resistance (EN 62262): IK08		
Gasket material:	TPE		Electrical insulation: Totally insulated		
Temperatures:			Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °C (short term):	-40 ... 120 °C		UV resistance: UL 508		
Temperature °C (continuous):	-40 ... 80 °C		Flammability Rating: UL 746C 5V		
Temperature °F (short term):	-40 ... 250 °F		Glow Wire Test (IEC 695-2-1) °C: 960		
Temperature °F (continuous):	-40 ... 175 °F		NEMA Class: NEMA 1, 4, 4X, 6		
Accessories:			Certificates:		
MIV 125	Mounting plate (Galvanized steel)		Germanischer Lloyd (GL)		
			SGS Fimko		
			Gost R		

