

Mains Dimmable LED Drivers - 66W to 80W Constant Voltage series



Short circuit, over current and over voltage protection
up to 80% efficient

- Fire resistant plastic cover
- Compatible with leading and trailing edge dimmers
- 10 ~ 100% Triac dimmable
- Mains dimmable
- Screw terminals for easy installation
- IP44 design for indoor use
- 2 years warranty



Please note dimming results vary according to quality of dimmer switch used. We recommend a high quality low load dimmer such as the Varilight Eclique series

Specification

INPUT	Voltage	180V ~ 240VAC	
	Frequency	50-60 Hz	
	Current	0.89A	
	Power Factor	0.95	
OUTPUT	MODEL No.	PAX1280TD	PAX2480TD
	Load Voltage	12V	24V
	No Load Voltage	12V	24V
	Current	5.5A	3.3A
	Power	80W	80W
	Power Factor	>0.95	
	Ripple & Noise	4V	4V
	Efficiency (TYP.)	>80%	
PROTECTION	Over Load	Auto-recovery	
	Short Circuit	Auto-recovery	
	Over Voltage	Auto-recovery	
ENVIRONMENT	Operating Temperature	-30 ~ +45°C	
	Storage Temperature	-40 ~ +70°C	
	Relative Humidity	5 ~ 95%	
SAFETY & EMC	Safety Standard	Design refers to EN60598, EN61547, ENV5024, EN61000-4-2, 3, 4, 6, 8, 11, EN61000-3-2, EN61000-3-3	
	EMI Standard	Meets Emissions to EN55022, EN55015 Class B	
OTHERS	Lifetime	50K hrs at TC max	
	Packing	503g	

