

9001KR5R

PUSHBUTTON OPERATOR 30MM TYPE K

+OPTIONS

List Price \$81.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Approvals	UL File Number E42259 CCN NKCR - CSA File Number LR24590 Class 3211-03 - CE Marked
Bezel Material	Chromium Plated Metal
Button/Cap Color	Red
Button Type	Snap-In Plastic Mushroom (2.25 Inch/57mm)
Guard Type	No Guard
Contact Configuration	No Contact Blocks
Enclosure Type	Water tight, Dust tight and Oil tight (Indoor/Outdoor)
Enclosure Rating	NEMA 1/2/3/3R/4/6/12/13
Head Type	Round
Light Module Supply Voltage	n/a
Light Module Type	n/a
Markings	None
Maximum Voltage Rating	600V
Mounting Type	Panel
Number of Operators	1
Number of Positions	2
Operator Action	Momentary
Operator Type	Non-Illuminated
Size	30mm
Type	K

Shipping and Ordering

Category	21426 - Push Buttons, 30 mm, Metal, Round, Type K
Discount Schedule	CS1
GTIN	00785901887317
Package Quantity	1
Weight	0.26 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.