



Lens,flat,with inscription

Part no.
Article no.
Catalog No.

M22-XDL-W-X1
218296
M22-XDL-W-X1Q

Delivery programme

Product range			RMQ-Titan (drilling dimensions 22.5 mm)
Basic function			Accessories
Single unit/Complete unit			Single unit
Description			 5 characters: letter height 5 mm > 5 characters: letter height 3 mm
Design			Flush
Name			START
For use with			M22(S)-DL-X M22(S)-DRL-X M22S-DGL-X
Colour, symbol			
Connection to SmartWire-DT			no

Approvals

North America Certification

UL/CSA certification not required

Technical data ETIM 5.0

Low-voltage industrial components (EG000017) / Legend plate for control circuit devices (EC000621)
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Button plate for command and alarm devices
(ecI@ss8-27-37-12-24 [AKF042010])

Shape			Round
Construction type			Flat
Colour			White
Imprint			-
Imprint ISO symbols			Symbol "I"
Engraveable			No
Programme diameter		mm	22
Width		mm	0
Height		mm	0
Outer diameter		mm	22
Suitable for push button			No
Suitable for illuminated push buttons			Yes
Suitable for indicator light			No
Mushroom head push button			No
Suitable for signalling lamp			No
Suitable for selector switch			No

Additional product information (links)

IL04716002Z (AWA1160-1745) RMQ-Titan System	
IL04716002Z (AWA1160-1745) RMQ-Titan System	ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL04716002Z2013_08.pdf
Labeleditor	http://downloadcenter.moeller.net/de/software.f6023a63-5acb-42c7-a51c-ccf99091cace