











ES-457 PoE ETHERNET TO SERIAL DEVICE SERVER Ethernet 2 Port RS232 Power Over Ethernet PoE

CONNECT, CONFIGURE, CONTROL YOUR SERIAL DEVICES



Features

- 2 Port RS-232 with Power over Ethernet IEEE802.3af
- Ethernet to Serial Device Server
- Data rate from 110 to 1,000,000 baud
- User friendly interface, simple to use, powerful in operation
- Serial Port Tunnelling allows serial cable replacement over any distance, no software required
- Optional DIN rail mounting kit





Description

Ethernet to Serial device server with Power over Ethernet providing access to two RS232 serial ports. Data transfer rates up to 1,000,000 baud, coupled with 1Mbit/s line drivers deliver uncompromising performance. Power over Ethernet PoE uses IEEE 802.3af standard.Our ES range provides simple instant networked serial ports. A web interface allows secure configuration and control of the serial ports over a local network or the internet using any browser. For Windows our in-house designed 32 bit and 64 bit driver gives you local COM ports, retaining existing software applications and allowing you to connect across your network to remote devices just as if they were attached locally. Serial Port Tunnelling individually configurable allows serial cable replacement over any distance, no software required. You can access the device via TCP/IP sockets from any networked device like an Android tablet, PC or phone. On Windows OS TCP/IP sockets are handled by the Winsock API, this will differ on other OSs.

Extend your reach! Remote serial devices with local control. With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!


Example Application







ES-457 Ethernet 2 Port RS232 Power Over Ethernet PoE

Box Information







Status LED	Green	Device Ready
	Flashing Yellow	Changing Settings
	Flashing between Red & Green	Querying IP
	Flashing Green/Red	User performing Hard Reset
	Flashing between Green & Red/Yellow	IP address diagnostic
	Flashing between Green & Yellow	Initialization diagnostic
Serial Port LEDs	Green light on	Port Open
	Flashing Green	Data RX / TX
Network LED	Green light on	Link Established
	Flashing Green	Data RX / TX

Port

Ports 2 port RS232

Connector DB9 Connector - 9 Pin Male

Power Input Power Over Ethernet OR 5 - 30V DC input, reverse polarity protected

Power Consumption 1.85W Typical

+44(0) 151 220 2500 sales@brainboxes.com www.brainboxes.com

ES-457 Ethernet 2 Port RS232 Power Over Ethernet PoE

Port Settings - RS232

Baud Rate From 110 - 1,000,000 1 MegaBaud

Data Bits 5,6,7 or 8

Parity Odd, Even, None, Mark or Space

Stop Bits 1 or 2

Flow Control RTS/CTS, DSR/DTR, XON/XOFF

Tx/Rx Modes Point to Point

Port Settings - Ethernet

Data Rate 10/100 Mega bits/second

Cabling Normal / Crossover auto-sensing (Auto-MDIX)

Power over Ethernet Power Over Ethernet IEEE 802.3af standard OR 5 - 30V DC input, reverse polarity protected

Environmental

Operating Temperature 0°C to $+55^{\circ}\text{C}$ / $+32^{\circ}\text{F}$ to $+131^{\circ}\text{F}$

Ambient Relative Humidity 5 to 95% (non-condensing)

Housing IP-30 rated case

Software

Network Protocols ICMP, IP, TCP, UDP, DHCP, BOOTP, Telnet, HTTP, RFC2217

Data Transfer Protocol TCP

Configuration Options Windows Utility, Web Interface

OS Compatibility Microsoft Windows 7 32 bit 64 bit Editions / Windows Server 2008 32 bit 64 bit Editions / Windows Vista

32 bit 64 bit Editions / Windows Server 2003 32 bit 64 bit Editions / Windows XP 32 bit 64 bit Editions /

Microsoft Windows 2000 / Fully RFC2217 compliant / Interface for other OS's & Linux

Approvals

Industry Approvals AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA

Microsoft Approvals

Microsoft Certified Gold Partner

Windows 8 32 bit 64 bit Editions
Windows 7 32 bit 64 bit Editions















Packing Information

Packaging Quick Start Guide, Installation CD including manual, Microsoft signed drivers & utilities

Device Ethernet 2 Port RS232 Power Over Ethernet PoE

Accessory Items Available from Brainboxes: Optional Global Power Supply - PW-800, DIN-Rail Mounting Kit - MK-048

Packaged Weight 0.240 kg, 8.47 ounces

Packaged Dims 160x135x45 mm, 6.3x5.3x1.8 inches

+1 855 958 2502 sales@brainboxes.com www.brainboxes.com

ES-457 Ethernet 2 Port RS232 Power Over Ethernet PoE

Product Support

Warranty Lifetime - online registration required

Support Lifetime Web, Email and Phone Support from fully qualified, friendly staff who

work in and alongside the Product Development Team





Additional Information

OEM option Available for bulk buy OEM

Made In Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards

'Manufacturer of the Year'

Customisable Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info:

sales@brainboxes.com

Accessory Items

ORDER CODE - DIN-Rail Mounting Kit - MK-048



ORDER CODE - Optional Global Power Supply - PW-800



+44(0) 151 220 2500 sales@brainboxes.com www.brainboxes.com