

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0192030145
Status: Obsolete
Description: Krimptite™ Temp-Term Steel Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 6

Documents:
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
Series 19203
Crimp Quality Equipment Yes
Mil-Spec N/A
Product Name Krimptite™, Temp-Terms
Type Ring

Physical

Barrel Type Closed
Insulation None
Material - Plating Mating Tin
Packaging Type Bag
Stud Size 6 (M3.5)
Wire Size AWG 18, 20, 22
Wire Size mm² 0.25 - 1.50

Material Info

Old Part Number A-S-132-06



Series
image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

19203Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description	Product #
Hand Crimp Tool	0640030100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100