



Pin Hole Layout
(Jack Bottom View)

| | | | | | | | | |
|-------------|----------------------------------|-----------------|---|--------------|---------------------|-------------|--------------|--------------------|
| 4 | BODY | Fe | | | | | | |
| 3 | FERRULE | Fe | | | | | | |
| 2 | DIELECTRIC | BAKELITE | TOLERANCE | | SIGNATURES | | DATE | |
| 1 | PIN | BRASS | 0 - 10 ±0.05 10 - 99 ±0.5 100 - 999 ±10.0 1000 - 9999 ±100.00 10000 - 99999 ±1000.00 | | DRAFT: ZHOU XIN GOU | | 28-03-2014 | |
| ITEM | DESIGNATION | MATERIAL | | | CHECKEO: | | 今入企业股份有限公司 | |
| REV | PART NO. & SAMPLE NO. | DATE | BY | | APPROVAL: | | TITLE | PAL Jack, PC Mount |
| A | JR-1780 | | | SHEET | SCALE | UNIT | REV | |
| B | | | | OF | 1:1 | mm | ∅ | CUSTOMER |