



Features:

- Universal / Full range AC input
- Works with all Apple & Andriod products
- Multiple USB Outputs
- Small & Compact Design
- MTBF >50,000 hours
- 1 Year Warranty



Output Characteristics	
Part Number	T5710ST
Voltage	+5V
Current Max.	10A
Current Min.	0A
Leakage Current	0.25mA @ 264Vac
No. of Outputs	8
Output Type	USB 2.0
Ripple & Noise (mV p-p)	240mVp-p
Protections	Over Current: Output shall hiccup until fault is removed Short Circuit: Output shut down and auto restart
Case Size (See below) mm	180mm x 60mm x 34mm

Input Characteristics	
Rated Input Voltage	100-240Vac
Full Input Voltage Range	90-254Vac
Rated Frequency	50-60Hz
Full Frequency Range	47-63Hz
Efficiency (avg.)	76%
Input Type	C8 Socket

Safety, Mechanical and Other Characteristics	
Range Model Designations	HC501-8U
Operating Temperature	0°C to 40°C
Storage Temperature	-10°C to 70°C
Operating Humidity	10% to +90%
Storage Humidity	5% to 95%
PB-free	Yes. RoHS Compliant
MTBF	50K Hours (mean time before failure)



Stontronics Ltd

Chancerygate Business Centre, Cradock Road, Reading, Berkshire, RG2 0AH.

Tel: +44 (0) 118 931 1199 • Fax: +44 (0) 118 931 1145 • Email: info@stontronics.co.uk • Web: www.stontronics.co.uk

Please Note: Image shown is representative of entire range. Individual PSU image &/or drawings or data sheets available on request.

Stontronics Ltd accepts no responsibility for typographical errors in the production of this leaflet. Product specifications are subject to change without notice.

Case Drawings:

T5710ST:

