

Protect It! 6-Outlet Surge Protector, 6-ft. cord, 900 Joules, Diagnostic LED

MODEL NUMBER: TLM606



Highlights

- 6 outlets / 6 ft. cord
- 900 joule rating
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for personal computers, TV/VCR/DVD, stereos, power tools and lamps/lighting

Package Includes

- TLM606 surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's TLM606 surge suppressor offers complete AC surge suppression for comprehensive protection of personal computers, home stereos, televisions, VCRs, DVD players, power tools and other electrical and electronic equipment. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLM606 offers 6 total outlets, a 6 foot power cord and diagnostic LED to warn of suppressor damage. AC surge suppression rated at 900 joules shields equipment from surges and line noise. Rugged metal housing offers convenient protection of desktop computer equipment and accessories. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

PLUG/OUTLETS: Input - 6 ft. AC line cord with NEMA 5-15P plug/Output - 6 NEMA 5-15R outlets

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA 5-15R wall receptacle)

FORMAT: Metal strip

SUPPRESSION: AC: 150V RMS Clamping/900 joules/330V UL1449 3rd Edition

Features

- 6 outlets
- 6 ft. cord
- Surge suppression rating: 900 joules
- EMI/RFI noise filtering
- Diagnostic LED confirms suppressor "protection present" (green)
- Convenient keyhole slots allow secure mounting on wall or desk
- Can accommodate up to 1 transformers without blocking adjacent outlets
- Rugged metal case provides extra safety and durability
- Illuminated on/off switch with integrated 15 amp circuit breaker
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

Specifications



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 1 large transformer without covering adjacent outlets
Outlet Orientation	Single row of outlets
USB Charging	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	45000
USER INTERFACE, ALERTS & CONTROLS	
Switches	Illuminated on/off switch with integrated 15 amp circuit breaker
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	900
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150V
UL1449 Let Through Rating	330V - UL Verified
EMI / RFI Filtering	Up to 20dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No



PHYSICAL	
Shipping Dimensions (hwd / in.)	1.75 x 15.5 x 4.5
Shipping Dimensions (hwd / cm)	4.4 x 39.4 x 11.4
Shipping Weight (lbs.)	1.6
Shipping Weight (kg)	.7
Unit Dimensions (hwd / in.)	1.5 x 12.5 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 31.8 x 6.3
Unit Weight (lbs.)	1.4
Unit Weight (kg)	.6
Material of Construction	Metal top enclosure, plastic bottom insert
Integrated Keyhole Mounting Tabs	Keyhole slots enable mounting to a variety of surfaces
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Form Factors Supported	Supports floor / wall / desktop placement
Outlets Measurement (Center to Center)	38.89mm
Keyhole Slot Mounting Measurement (Center to Center)	165mm
Metal Case	No
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
Additional International Approvals	Complies with RoHS (Restriction of Hazardous Substances Directive)
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance
---	---

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>