

## Heavy-Duty Power Extension Cord, 15A, 14AWG (IEC-320-C14 to IEC-320-C13), 1-ft.

MODEL NUMBER: **P005-12N**



### Highlights

- C13 to C14 Power Cable, 1-ft. (12 in.)
- 14 AWG x 3C
- 15A / 100 - 250V
- RoHS Compliant
- UL Listed

### Package Includes

- C13 to C14 Power Cable, 1 ft. (12 in.)

### Description

Use Tripp Lite's P005-12N in server applications that require a high-rated, heavy-gauge cable. Its short length is perfect for server to PDU or UPS connections that are in close proximity. C13 to C14 connectors, 3 x 14 AWG conductors, 15A rating and 100-250V.

### Features

- Short length reduces rack cable clutter
- Molded, heavy-duty power cable, 1 ft. (12 in.)
- IEC-320-C13 to IEC-320-C14
- 14 AWG x 3C, SJT, 15A, 100-250 Volt
- RoHS Compliant
- UL Listed

## Specifications

INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C14



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Connector B	IEC-320-C13
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>