



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Heavy-Duty Y Splitter Power Cord for PDU and UPS, 20A, 10AWG (NEMA L6-20P to 2x NEMA L6-20R), 1 ft.

MODEL NUMBER: **P039-001-2**



Highlights

- L6-20P to 2 x L6-20R Power Splitter
- 10AWG x 3C, 20-Amp, 250V
- RoHS Compliant

Package Includes

1-ft. L6-20P to 2 x L6-20R Power Splitter Cord

Description

Tripp Lite's Power Splitter Cord - L6-20P male to 2 x L6-20R female. Constructed with 3 x 10ga copper conductors, fully molded ends and 250V/20A rating.

Features

- Molded, Heavy-Duty Power Splitter Cord, 1ft.
- NEMA L6-20P to 2 x NEMA L6-20R
- 10AWG x 3C, SJT, 20A, 250Volt
- RoHS Compliant

Specifications

INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA L6-20P
Connector B	NEMA L6-20R (X2)
Number of Connectors	3



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>