



Overview

Plas-Fix® 60 - Pan CR (Z) (PR60)

Three-lobed threadform

Imperial dimensions

Materials and Finishes

Steel/Zinc & clear de-embrittled

Stainless Steel/Self colour (Please enquire for availability)

Please note: Not all sizes stated are available from stock, please enquire for availability.

Note: Due to the fact that fastening applications differ greatly, the below information is for guidance only and is correct to the best of our knowledge. The customer must satisfy themselves with the performance of the fastener and validity of the data. TR Fastenings will not be held responsible for any failure that may occur from the use of this information

Dimension Data

Dia. Gauge	N2 (2-28)	N4 (4-20)	N6 (6-19)	N8 (8-16)	N10 (10-14)
Dia. d1 Max	0.089	0.123	0.143	0.179	0.208
D	0.167	0.219	0.270	0.322	0.373
K - Max	0.062	0.080	0.097	0.115	0.133
Recess	1	1	2	2	2

Part number	Finish	Length	Material	Thread
W/N6/0.625/PRST60/TC1D	Zinc Trivalent Clear De-embrittled	16.0mm (5/8")	Steel	3.5mm (No.6)