

## Husky Pup<sup>RB4XMV/2P</sup>



18cd (light amber)	75 flashes/min	10–100Vdc 20–72Vac	145mA	40mA	IP65	0.4kg

### Features:

A bright, multivoltage 2W Xenon beacon.

- Multivoltage 10 – 100 Vdc, 20 – 72 Vac
- Bright, intense Xenon flash
- Ultra-low power consumption
- 3,000+ hours tube life, 12 months' guarantee
- Weatherproof to IP65

### Product options:

- European 130mm PCD hole pattern to ISO 4148
- US 118mm (4 5/8") PCD hole pattern
- Sounder plinth, fixes to base of beacon

CE – certified to EMC directive 89/336/EEC.

Complies with low voltage directive 73/23/EEC.

High voltage transient and polarity reversal protected.

Operating temperature: –20°C to + 55°C.

Beacon should be operated in a vertical position with lens uppermost.



FX29 Sounder Plinth  
Part No. 521047

### Applications:

Suitable for fork lift trucks and battery powered vehicles.

### Materials:

Polycarbonate lens, ABS base.

Lens Colour	Three Bolt Europe	Three Bolt USA	Magnetic	Pole Mount
Amber	469040	469062	469086	469082
Red	469041	469063	–	–
Blue	469042	–	–	–
Clear	469039	–	–	–
Green	469043	–	–	–
	<p>Drilling for Panel Mounting (ISO 4148)</p> <p>4 holes 7mm dia. 120° 120° Cable entry 130 mm dia.</p>	<p>Drilling for Panel Mounting (USA Hole Pattern)</p> <p>4 holes 6mm (0.236ins) dia. 120° 120° Cable entry 118 mm dia.</p>		