


The supplier acknowledges that, with the acceptance of the drawing, he is in a position to manufacture the illustrated part in accordance with the drawing in reproducible form and series production. Through the selected manufacturing processes no impairments will arise in the material and structure which could subsequently lead to an impairment of the component. Verbal agreements over and above that are not valid. Deviations from this rule must be written and must be signed by the purchaser.



Technische Daten/  
technical data

- Leuchtmittel/  
illuminant : Nichia LED
- Lebensdauer/  
Life-time : ca./approx. 50.000h
- Zellenzahl/  
number of cells : 2x AAA Micro, included
- Leuchtweite  
beam : 35m
- Leuchtdauer  
operating time : 12h
- Helligkeit/  
brightness : 20 Lumen
- Gehäuse/  
housing : Aluminiumgehäuse, schwarz eloxiert/  
aluminiumhousing, black anodized
- Gewicht/  
weight : 64g inkl. Batterien/  
incl. batteries
- Verpackung/  
package : Farbige Kartonbox/  
colored carton box
- Approbation/  
approval : CE
- Schutzklasse/  
protection class : IP54

Verwendungsbereich/Application range für Anfrage/for inquiry AN201354				Zul. Abweichung/ Allowable deviation	Oberfläche/ Surface	Maßstab/Scale (DIN A4): 1:1	Gewicht/Weight
				general tolerances DIN ISO 2768-m		Werkstoff/Work material, Modell-Nr.	
				2013 Erstellt/ Drawn by	Datum/Date 22.08	Name KA	
				Zeichnungsname/Drawing name			
				AGENT Profi-Penlight			
V2	printing added	19.01.15	SIT	Zeichnungsnummer/Drawing number Artikelnummer/Part number			Blatt/ Sheet
V1	lanyard added	20.01.14	CF	1600-0067			1
V1	date code changed and address added	20.01.14	CF				
V0	---	22.08.13	KA				
Version	Änderung/Change	Datum/Date	Name	Ursprung/Origin	Proj. XX/XX/XX	Ersatz für/Replaced by	Ersatz durch/Replacement through: