

# DE2E3KY222MA2BM01F

"#" indicates a package specification code.
















< List of part numbers with package codes > DE2E3KY222MA2BM01F

#### Shape



#### Notes

X1/Y2 Class Certified Products, Halogen-free Products

#### References

Packaging	Specifications	Minimum quantity
В	Packing in bulk	250

### Specifications

Capacitance	2200pF ± 20%
Rated voltage	250Vac(r.m.s.)
Temperature characteristics (complied standard)	E(JIS)
Capacitance change rate	+20/-55%
Temperature range of temperature characteristics	-25 to 85
Operating temperature range	-40 to 125

1 of 2

## **Attention**

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it 's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




Murata Manufacturing Co., Ltd.


URL: http://www.murata.com/

Last updated: 2015/08/17

Frequency characteristics (ESR, Impedance)




DC bias characteristics




Capacitance - temperature characteristics

This PDF data has only typical specifications because there is no space


for detailed specifications.



S parameter (Smith chart S11)



AC voltage characteristics



2 of 2

Last updated: 2015/08/17