

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050841150

Status:

Active

Overview:

MLX™ Power Connectors

Description:

2.13mm Diameter MLX™ Power Crimp Housing Plug, 15 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-42022-0001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	42021
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 36643-0008. Current – Maximum per contact 20A if used with 36663 and 36664 terminal
Overview	MLX™ Power Connectors
Product Name	MLX™
UPC	800753755291
Physical	
Circuits (maximum)	15
Circuits Detail	15
Color - Resin	Natural
Flammability	94V-2
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	8.113/g
Number of Rows	5
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55°C to +105°C
Electrical	
Current - Maximum per Contact	11.0A, 20.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	42021-15A
Reference - Drawing Numbers	
Product Specification	PS-42022-0001
Sales Drawing	SD-42021-**



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(17. December 2014):

No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

42021 Series

Mates With

42002 MLX™ Power Connector Header, 42022 MLX™ Pin and Socket Receptacle, 43255 MLX™ Power Connector Header

Use With

MLX™ Crimp Terminal 36663 , 36664 , 42023 , 42024

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION