

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009508031

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 3.96mm Crimp Terminal Housing, Friction Ramp, 3 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-08-50 (PDF)

Packaging Specification PK-41695-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	41695
Application	Power, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 396
UPC	800753613782
Physical	
Breakaway	No
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.053/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	41695-N-B3
Reference - Drawing Numbers	
Packaging Specification	PK-41695-001
Product Specification	PS-08-50
Sales Drawing	SD-41695



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2015

June 15): Yes

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

41695 Series

Mates With

KK® 396 Header [41791](#) , [41792](#) , [41671](#) , [41672](#) , [41661](#) , [41662](#)

Use With

KK® 396 Crimp Terminals, [2478](#) , [2578](#) , [6838](#) , [7258](#) , [45570](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION