

Round Plastic Spacer / Length +/- 0.1 mm

05.84.150

Product No. **05.84.150**

Model	Plastic Spacers
Type	Standard, cut ends
Design	molded
Inner Diameter	for M4- Dia. 4.1-4.5
Outer Diameter	8.00 mm
Length	15.00 mm
Material	Nylon, 25% glass-fiber reinforced UL94 HB
Plating	Black
UL Flammability	UL94 HB
Attributes / ID Ø	4,2 mm
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products Round Spacer ø4.2/8.0x15.0mm
Polyamid 6.6, natural
05.84.156
Round Spacer for M4 metric screws;
4.2/8.0X15.0; polystyrene; natural
07.24.815

