

**Cable Clamp  $\varnothing 7.0\text{mm}/16.5 \times 8.0\text{mm}$  Steel, zinc-plated/hole  $\varnothing 3.6\text{mm}$**   
14.42.907

Product No. 14.42.907

<b>Model</b>	U-Clamps
<b>Type</b>	Screw mount one-sided
<b>Design</b>	Standard
<b>Holding Diameter</b>	7.00 mm
<b>Material</b>	Steel
<b>Mounting Hole</b>	3.60 mm
<b>Color</b>	Zinc-plated
<b>Broad</b>	8.00 mm
<b>Lenght - L</b>	16.50 mm
<b>Distance M/M</b>	8.50 mm
<b>RoHS II compliant</b>	yes
<b>Reach/SVHC free</b>	yes

