



**HBL18221CN****HBL® Extra Heavy Duty Industrial Series
15A, 347V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle, back and side wired.	Brown Ivory	HBL18201CN	—	HBL18203CN	—
		HBL18201ICN	—	HBL18203ICN	HBL18204ICN
Locking.		HBL18201LCN	—	HBL18203LCN	—
Key for Locking switch.		HBL1209*			

**HBL® Extra Heavy Duty Industrial Series
20A, 347V AC**


Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle, back and side wired.	Brown Ivory	HBL18221CN	—	HBL18223CN	—
		HBL18221ICN	—	HBL18223ICN	HBL18224ICN

**HBL1281****PresSwitch® Specification Grade Push Button, Standard Type
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon actuator, side wired only.	Brown Ivory	HBL1281 HBL1281I	HBL1282 HBL1282I	HBL1283* HBL1283I*	HBL1284* HBL1284I*

**Momentary Type•
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Circuit normally closed, side wired only.	Brown	HBL1281MC*	—	—	—
Circuit normally open, side wired only.	Brown	HBL1281MO*	—	—	—

**HBL1297****Illuminated and Pilot Light PresSwitch®,
120V AC Lighted Actuator, Light On with Load Off•**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
15A, nylon actuator.	Ivory	—	—	—	HBL1259I*
20A, nylon actuator.	Ivory	HBL1287I	—	HBL1288I*	—

**Pilot Light Actuator, Light On with Load On
20A, 120V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon actuator.	Red	HBL1297	—	HBL1298*	—

Note: Keys are supplied with each locking switch. For extra keys order HBL1209.

*Not UL Listed, CSA Certified.

•Not HP rated.

See page D-13 for accessories.

See page D-15 for wallplates.

See page D-20 for technical information.

Dimensions in Inches (mm)

HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP