



LED Maintenance Worklights

Description	Outlet Rating	Rating	Wattage	Lumen Output	Cord Type	Cord Length	Catalog Number
LED Industrial maintenance light	NA	15A 125V	28	2928	16/3 SJEOW	25 ft.	HBLML2825L
LED worklight with end light feature	NA	15A 125V	9	920/120	18/2 SJTOW	25 ft.	HBLWL25LED
LED worklight with end light feature and tool tap	12 Amp	15A 125V	9	920/120	16/3 SJTOW	25 ft.	HBLWL25LEDT



Fluorescent Maintenance Worklights

Description	Outlet Rating	Rating	Wattage	Lumen Output	Cord Type	Cord Length	Catalog Number
Fluorescent worklight with straight blade plug	NA	15A 125V	13	825	16/3 SJTOW	25 ft.	TW25F1
Fluorescent worklight with Twist-Lock® plug and tool tap	12 Amp	20A 125V	13	825	16/3 SJTOW	25 ft.	TW25F2
Fluorescent maintenance light, 34.5 in.	NA	15A 125V	50	3750	16/3 SJEOW	25 ft.	HBLML5025
Fluorescent maintenance light, 48.5 in.	NA	15A 125V	25	2125	16/3 SJEOW	25 ft.	HBLML2525
Fluorescent worklight, 45 in.	NA	15A 125V	25	2125	16/3 SJTOW	25 ft.	HBLWL2525



Accessories

Description	Catalog Number
Magnetic mounting bracket for ML style lights, 82 lb. capacity	HBLMLMM
Magnetic mounting bracket for WL style lights, 58 lb. capacity	HBLWLMM
Replacement rough service fluorescent bulb for 13 watt style lamps	HBLREPPFB



Explosion Proof/Confined Space Lighting

Hazardous Location Lights

Description	Wattage	Lumen Output	Cord Type	Cord Length	Catalog Number
Fluorescent, Class 1, Div 1 Groups C & D, Class 2, Div 1 Groups F & G, 12V, inline transformer	26	1800	16/3 SOW	60 ft.	HBLXF6012V
Incandescent, Class 1, Div 1, Groups C & D, 12V, inline transformer	75	720	16/3 SOW	60 ft.	HBLXI6012V
Fluorescent, Class 1, Div 1 Groups C & D, Class 2, Div 1 Groups F & G, 120V, less plug	26	1800	16/3 SOW	50 ft.	HBLXF50120V
Incandescent, Class 1, Div 1 Groups C & D, 120V less plug	100	1230	16/3 SOW	50 ft.	HBLXI50120V
Fluorescent, non-explosion proof, wet location, 12V, inline transformer	13	825	18/2 SJTOW	60 ft.	HBLWT6012V



Cordless Hazardous Location Light

Description	Wattage	Lumen Output	Rating	Catalog Number
Intrinsically safe, Class 1, Div 1 Groups C & D, with universal charger	9	378	4.8V	HBLIS300

