

IP66*
 SUITABILITY

Straight Male

	NPT Hub Size	Cord Dia. Inches (mm)	Form Size	Color Code	Machined Aluminum	Machined Zinc-Plated Steel	Stainless Steel	Nylon Gray	Nylon Black
 Machined Aluminum	¼	.06"-.13" (1.6-3.2)	F1	Green	—	—	—	SHC1001CR	—
		.13"-.19" (3.2-4.7)		Orange	SHC1002	—	—	SHC1002CR	—
		.19"-.25" (4.7-6.3)		Red	SHC1003	—	SHC1003SS	SHC1003CR	—
		.25"-.31" (6.3-7.9)		Black	SHC1004	—	SHC1004SS	SHC1004CR	—
		.31"-.38" (7.9-9.5)		White	SHC1005**	—	—	SHC1005CR	SHC2005CR
		.38"-.44" (9.5-11)		Blue	—	—	—	SHC1006CR	—
 Machined Zinc-Plated Steel	¾	.06"-.13" (1.6-3.2)	F1	Green	SHC1007	—	—	—	—
		.13"-.19" (3.2-4.7)		Orange	SHC1008	SHC1008ZP	—	SHC1008CR	SHC2008CR
		.19"-.25" (4.7-6.3)		Red	SHC1009	—	SHC1009SS	SHC1009CR	—
		.25"-.31" (6.3-7.9)		Black	SHC1010	SHC1010ZP	—	SHC1010CR	SHC2010CR
		.31"-.38" (7.9-9.5)		White	SHC1011	—	SHC1011SS	SHC1011CR	SHC2011CR
		.38"-.44" (9.5-11.0)		Blue	SHC1012	SHC1012ZP	SHC1012SS	SHC1012CR	SHC2012CR
 Stainless Steel	½	.19"-.25" (4.7-6.3)	F1	Red	SHC1015	—	—	—	—
		.25"-.31" (6.3-7.9)		Black	SHC1016	—	—	—	—
		.31"-.38" (7.9-9.5)		White	SHC1017	—	—	—	—
		.38"-.44" (9.5-11.0)		Blue	SHC1018	—	—	—	—
 Gray Nylon	½	.06"-.13" (1.6-3.2)	F2	Green	SHC1019	—	—	SHC1019CR	—
		.13"-.19" (3.2-4.7)		Orange	SHC1020	SHC1020ZP	SHC1020SS	SHC1020CR	—
		.19"-.25" (4.7-6.3)		Red	SHC1021	SHC1021ZP	SHC1021SS	SHC1021CR	SHC2021CR
		.25"-.38" (6.3-9.7)		White	SHC1022	SHC1022ZP	SHC1022SS	SHC1022CR	SHC2022CR
		.38"-.50" (9.7-12.7)		Blue	SHC1023	SHC1023ZP	SHC1023SS	SHC1023CR	SHC2023CR
		.50"-.63" (12.7-15.9)		Brown	SHC1024	SHC1024ZP	SHC1024SS	SHC1024CR**	SHC2024CR**
 Black Nylon	½	.38"-.50" (9.7-12.7)	F3	Blue	SHC1025	—	—	—	—
		.50"-.63" (12.7-15.9)		Brown	SHC1026	—	—	—	—
		.63"-.75" (15.9-19.0)		Yellow	SHC1027**	SHC1027ZP**	—	—	—
		.75"-.88" (19.0-22.2)		Orchid	SHC1028**	SHC1028ZP**	—	—	—

Note: See pages V-87 to V-95 for technical information and dimensional drawings.
 *IP66 Suitability when used with optional metal clad O-ring, see page V-84 for additional information.
 **Cable jacket may have to be stripped to pass through connector body.
 Locknuts sold separately. See page V-84 for additional information.