

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0701070005

Status:

Active

Overview:

SL™ Modular Connectors

Description:

SL™ Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 6 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-70400 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

Crimp Housings

70107

Signal, Wire-to-Wire

Version A without Mounting Ears

SL™ Modular Connectors

SL™

800753560819

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

6

Black

94V-0

Male

No

Yes

Polyester

1.160/g

1

Bag

No

2.54mm

Yes

No

-40°C to +105°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-70400

SD-70107-0001-0024



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(17.

December 2014): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

70107 Series

Mates With

70066 SL™ Crimp Housing A, G and D

(Notes: Version C and H will not mate

to the 70107 housing series), 70400

SL™ Insulation Displacement Connector

Assembly, Version G Housing, 70430 SL™

Single Row Receptacle, Version G

Use With

70021 SL™ Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION