

Torque range from 0.05 to 13.5 N.m

ESD Preset Torque Screwdrivers

Want to know how to use this tool?



Watch our video

For Bits & Blades... see pages 64-66 or visit www.torqueleader.com



ESD 25 & 150



ESD 450 & 1350



T-Bar



Key Benefits

- ▶ In addition to the main bullets on **page 13** the ESD 450 and 1350 models come with T-Bars as standard to assist with higher torque
- ▶ To allow for customisation and clear identification interchangeable coloured end caps are available in packs of four (Order Code: **065800**)
- ▶ ESD models are ideal for safe electronic component assembly as these are **EPA compliant**

Order now... call our Sales Hotline +44 (0) 1483 894 476

Order Code	Model	Range		Drive	k mm	g	Repeatability	ISO 6789 Class	T-Bar
		ISO	Imperial						
065405	ESD 25 FH	0.05 - 0.25 N.m	0.45 - 2.2 lbf.in		132	210	+/- 6%	2F	X
065415	ESD 25 FH O/W	0.05 - 0.25 N.m	0.45 - 2.2 lbf.in		132	224	+/- 6%	2F	X
065505	ESD 150 FH	0.2 - 1.5 N.m	1.8 - 13 lbf.in		132	210	+/- 6%	2F	X
065515	ESD 150 FH O/W	0.2 - 1.5 N.m	1.8 - 13 lbf.in		132	224	+/- 6%	2F	X
065605	ESD 450 FH	0.5 - 4.5 N.m	4.5 - 40 lbf.in		140	230	+/- 6%	2F	✓
065615	ESD 450 FH O/W	0.5 - 4.5 N.m	4.5 - 40 lbf.in		140	245	+/- 6%	2F	✓
065705	ESD 1350 FH	2.5 - 13.5 N.m	22 - 120 lbf.in		140	230	+/- 6%	2F	✓
065715	ESD 1350 FH O/W	2.5 - 13.5 N.m	22 - 120 lbf.in		140	245	+/- 6%	2F	✓



TLS Screwdrivers can be customised to your exacting requirements... why not discuss your options with us by calling now on **+44 (0) 1483 894 476**