

# New Hard Case Pro Work Light



## Features:

- New HC Visual Design Language
- Trouble Light form factor
- Hanger Hook
- Magnet
- 180° light output
- ABS 709 Material
- Optics: 6 mid-powered LED's (Nichia 757)
- Switching: Hi/Lo/Off
- 4xAA batteries included

## ANSI Claims\*:

	NEW
Light Output	350 High mode 50 Low mode
Run Time	6h Hi 25h Low
Beam Distance	235mt
Drop test	7mt
Water resistance	IPX4



## Codes:

- SAP – NEW 639825
- EAN – NEW 7638900398250
- ITF – NEW 17638900398257

Product Available **Q1 FY15**

**Energizer**

