

Handheld UV Magnifier
16401GY



U.V. PORTABLE MAGNIFIER 5D 3C

Idea for the inspection of conformal coatings. With a combination lightsource, coatings glow brilliantly especially when magnified through a 5-diopter (2.25X) optical-quality glass lens.

Old item no.: 16401GY



Lightsource	
Lamp power (W)	8
Lamp base	2 G 1 1
Number of lamps	4
Number of lamps 2	2
Lamp power 2 (W)	8
Lamp base 2	2 G 1 1
Lightsource	T 3
Lightsource 2	BLB

Optic	
Material of reflector	Aluminum
Primary Lens (D)	5
Magnification (X)	2
Working distance (mm)	2 0 3
Color of reflector	Mirror

Body	
Body color	Grey
Body material	Polycarbonate

Ballast	
Type of Ballast	Multi watt HF

Electrical data	
Maximum frequency (Hz)	6 0
Minimum frequency (Hz)	5 0
Maximum voltage (V)	1 2 0
Voltage from (V)	1 0 0
Total consumption (W)	1 6

Dimensions	
Net weight (kg)	0
Gross weight (lb.)	3

Technical data	
IP classification	2 0

Termination	
Cord length (ft)	8