



Main

Range	ClimaSys CV
Category	Top hood with fan
Type of filter	G2
Flow rate	Free flow rate : 575 m ³ /h at 50 Hz With outlet grille cut-out 291 x 291 mm : 350 m ³ /h
Input voltage	230 V 50/60 Hz

Complementary

Absorbed power	85 W
Noise level < at	64 dB
Height	External : 96 mm
Width	External : 340 mm
Depth	External : 340 mm
Cut-out dimensions	291 x 291 mm
Material	Steel for hood
Colour	Hood : grey RAL 7035
IP degree of protection	IP54
Device composition	1 fixing elements 1 fan 1 hood top of enclosure

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual