



Horizontal UK PDUs

Picture shows 6 way horizontal UK PDU

- 3-metre 1.5mm lead
- Tough 1.5U aluminium extrusion
- Shrouded switch with switch cover
- C14, C20, or 16A commando options
- Horizontal UK 13A BS1363 'type G' outlets

Horizontal UK PDUs are preferred by many due to the fact that it is commonplace for equipment to be fitted with a UK plug. Horizontal UK PDUs allow users to power essential equipment from one easy location in the rack

The cable exits the unit at the rear, making mounting of the PDU easier, whilst taking up only 1.5U of vital rack space

Standard products

Order Code	Product Description
H13A/4	4-way UK power with switch to 3-metre lead to 13A plug
H13A/4/F	4-way UK Filtered power with switch to 3-metre lead to 13A plug
H13A/5	5-way UK power with switch to 3-metre lead to 13A plug
H13A/5/F	5-way UK filtered power with switch to 3-metre lead to 13A plug
H13A/6	6-way UK power with switch to 3-metre lead to 13A plug
H13A/6/F	6-way UK Filtered power with switch to 3-metre lead to 13A plug


PDU options



IEC C14 plug
IEC 60320(320)



16A commando plug
IEC 60309(309)



IEC C20 plug
IEC 60320(320)

PDU technical data

Weight of PDU	1.1kg – 1.15kg
Net length of PDU	490mm
Net width of PDU	60mm
Net depth of PDU	45mm
Shipping length of PDU	520mm
Shipping Width of PDU	132mm
Shipping Depth of PDU	75mm
Shipping Weight of PDU	1.3kg – 1.35kg
PDU max power	3250W
Output rating	13A
Overall rating	16A
Input Frequency	50/60Hz
Acceptable Input Voltage	250VAC