



Schneider Electric USA
1415 South Roselle Road
Palatine, IL 60067
Customer Care Center: 1-888-778-2733
Web: www.schneider-electric.us

ITEM # LC1D40U7, OLD TYPE TESYS D IEC CONTACTOR - 40A - VAC COIL

TeSys D IEC Contactor - 40A - 240Vac Coil



Specifications	
Termination Method	Screw Clamp
Contact Rating	600V / 40A
Coil Voltage	240Vac 50/60 Hz
50/60 Hz Voltage Code	U7
Coil Consumption Inrush	220 VA
Coil Consumption Sealed	22 VA
Power Wire Size	#4 - #16 AWG
Power Terminal Torque	45 lb-in (5 Nm)
Control Wire Size	#10 - #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Mounting Hardware	35mm DIN Rail, #8 screw
Weight	3.11 lb (1.41 kg)
AC1 Resistive Rating	60 Amp
AC3 Single Phase 115V	3 HP

AC3 Single Phase 230V	5 HP
AC3 Three Phase 200V	10 HP
AC3 Three Phase 230V	10 HP
AC3 Three Phase 460V	30 HP
AC3 Three Phase 575V	30 HP
Control Contact Rating (1NC/0NO)	A600
UL File/CCN	E164862 / NLDX
CSA File	LR43364 3211 04
Meets Standard	IEC 60647-4
CE	Yes
RoHS	Yes