

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000041](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: Mini-Fit® Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Bag

Documents:

- [Drawing \(PDF\)](#)
[Product Specification PS-51010-005 \(PDF\)](#)
[Product Specification PS-51010-006 \(PDF\)](#)
[Product Specification PS-51096-001 \(PDF\)](#)
[Product Specification PS-52034-003 \(PDF\)](#)
- [Product Specification PS-52034-004 \(PDF\)](#)
[Product Specification PS-5556-002 \(PDF\)](#)
[Test Summary TS-5556-002 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0040 (Reel)
Product Name	Mini-Fit®
UPC	800753585034

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	123.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Old Part Number	5558TL
-----------------	--------

Reference - Drawing Numbers

Product Specification	PS-51010-005, PS-51010-006, PS-51096-001, PS-52034-003, PS-52034-004, PS-5556-002, RPS-30067-002
Sales Drawing	SD-5558****
Test Summary	TS-5556-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015 June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5558](#) Series

Mates With

[5556](#) Mini-Fit® Crimp Terminal

Use With

[5559](#) Mini-Fit Jr.™ Plug Housing, [30068](#) Mini-Fit® TPA Plug Housing, [42475](#) Mini-Fit® BMI Plug Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030044
Hand Crimp Tool for Male and Female	0638190900

Crimp Terminals, 16-24 AWG Wire Japan	
Description	Product #
Handtool (Straight Action)	<u>0570225500</u>
Hand Extraction Tool	<u>0570316000</u>
Hand Crimp Tool	<u>0570265000</u>

This document was generated on 09/10/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION