

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640014

Status:

Active

Overview:

Splices

Description:

Perma-Seal™ Butt Splice for 18-22 AWG Wire, Mylar Tape Carrier

Documents:

Drawing (PDF)

Product Specification PS-19902-015 (PDF)

Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19164
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Butt - Funnel Entry, Perma-Seal™
UPC	800753113022
Physical	
Barrel Type	Closed
Color - Resin	Red
Insulation	NiAc™
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.274/g
Packaging Type	Adhesive Tape on Reel
Temperature Range - Operating	-55°C to +125°C
Wire Insulation Diameter	5.33mm max.
Wire Size AWG	18, 20, 22
Electrical	
Voltage - Maximum	600V
Material Info	
Old Part Number	SAA-22-18T
Reference - Drawing Numbers	
Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19164-017



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2014

December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

PremiumGrade™

0640017400

Hand Crimp Tool

ATP Crimp Dies

0192880264

for the Tape Crimp

Module and ATP-101

& 301 Press

Power Crimp Tool

0640057400

Head for Terminals

10-22 AWG Wire

This document was generated on 09/10/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION