



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



BIT,AUGER,QUICK CHANGE 3/4A (POP)

3/4 Stubby Auger Wood Bit

Cat No: 52027523

UPC No: 783310124177

### Description

---

- Over center single flute design for cleaner holes and less splintering
- Unique cutting edge design for fast and smooth cutting action
- Shorter than the top competitor's bit for better access to tight spaces between studs and joists
- Perfect for drilling 2 IN and 4 IN joists
- Augers have self-feeding screw point that draws bit through all wood types with less operator fatigue
- Eliminates the need for special tools such as expensive right angle drills or multiple steps to cut the hole to size
- 1/4 IN hex quick change design for fast and easy use in all drill types
- Clearly marked with bit diameter and catalog number on shank for easy identification

### Specifications

---

- Application : For Drilling 2.000 IN And 4.000 IN Joists And Wood
- Bit Diameter : 3/4 IN (19.100 MM)
- Overall Length : 4.500 IN (144.000 MM)
- Shank Diameter : 1/4 IN
- Shank Type : Hexagonal
- Type : Stubby, Quick Change
- Weight : 0.300 LB (136.000 GM)