

BU-32614-*
(Stackable, Retractable Banana Plug)



The BU-32614 has a spring loaded retractable sheath that provides electrical protection when the cable is not mounted and slides into the housing when pressed into a non-shrouded jack. It also has a built-in banana jack that allows stacking other test leads with retractable or unshrouded 4mm banana plugs.

- Fits all standard 4mm Banana Jacks
- Easy solder connection with wire between 14-18 AWG
- Material: Housing – Nylon
Contact – Brass and Beryllium Copper
- Colors: designated by "*" in the part number: -0 black, -2 red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- Ratings: 20 Amps, Hands free testing up to 1000V. @105°C
- RoHS Compliant