



**Mallory Sonalert Products, Inc.**

Part #:

**SBS300FL**

**Sales Outline Drawing**

Revision:

**A**

**Specifications:**

**Medical Spec IEC60601-1-1-8**

Coil Impedance ( $\Omega$ ):	8 @ 1-Volt
Rated Voltage (V):	2.8Vp-p Square Wave
Power Rating (W):	1W Rated 1.5W Max.
Recommended Drive Frequency:	325 Hz
Loudness @ 10 CM:	95 to 105 dB(A) Typ.
Harmonics Present:	Minimum of 4 peaks within $\pm 15$ dB from 1-4kHz
Housing Material:	ABS 777D Plastic Resin, Black
Leading Wire:	28 AWG
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight (Typical):	0.56 oz (16 g)
Options:	Please contact factory.

**Dimensions:** mm

**ROHS Compliant**

