

Safety Padlocks

BradyID.com/lockouttagout

Lockout Tagout



Actual size of Brady's Compact Safety Padlock



Compact Safety Padlocks

- Extremely compact and lightweight - the smallest safety lock on the market
- Easily fits in small spaces - ideal for electrical contractors/maintenance/electricians
- 5-pin cylinder can support same keying system as our current Safety Padlock
- Fiberglass reinforced nylon body for extra impact resistance
- Service temperature: 0°–250° F (-20°–120° C)
- Lock body dimensions: 1-2/5"H x 1-1/5"W x 5/8"D
Shackle clearance: 1"; shackle diameter 1/5"
- Each padlock includes 1 key and 1 each English, Spanish and French labels

Compact Safety Padlocks - 1" Steel Shackle

Color	Keyed Different 1/Pack	Keyed Different 6/Pack	Keyed Alike 3/Pack	Keyed Alike 6/Pack
Red	143150	118926	118953	118954
Green	143152	118927	118955	118956
Orange	143154	118928	118957	118958
Blue	143156	118929	118959	118960
Yellow	143158	118930	118961	118962
Brown	143160	118931	118963	118964
White	143162	118932	118965	118966
Purple	143164	118933	118967	118968
Black	143166	118934	118969	118970

Brady Safety Padlocks

- Comply with all OSHA requirements and are a safer alternative to metal locks for lockout applications
- Nonconductive body with unique key cylinder prevents electricity from traveling from the shackle to the key, protecting workers when key is inserted
- Superior temperature, chemical and corrosion resistance
- "Danger" and "Property of" labels provided in English, Spanish and French and printed on 100% recycled paper
- Reserved paracentric keyway provides optimal security (prevents someone from getting a copy made at a local key shop)
- Key-retaining feature prevents key from being removed until shackle is securely closed
- Locks come keyed differently or in keyed-alike sets. Custom keying and charting available
- Lock bodies can be custom laser engraved upon request
- One key is supplied with each padlock for safer key management



Safety Padlocks

- Lightweight, nonconductive and non-sparking body
- Special 6-pin cylinder resists tampering
- Fiberglass reinforced nylon body and triple-coated hardened steel shackle
- Service temperature: 0°–250° F (-20°–120° C)
- Lock body dimensions: 1-3/4"H x 1-1/2"W x 4/5"D
- Shackle clearance: 1-1/2"; shackle diameter: 1/4"
- Each padlock includes 1 key and 1 each English, Spanish and French labels

Safety Padlocks - 1-1/2" Steel Shackle

Color	Keyed Different 1/Pack	Keyed Different 6/Pack	Keyed Alike 3/Pack	Keyed Alike 6/Pack
Red	99552	51339	105886	105890
Green	99564	51345	105889	105893
Orange	99576	51347	123268	123270
Blue	99556	51344	105887	105891
Yellow	99570	51346	105888	105892
Brown	103033	101956	118947	118948
White	143123	118925	118949	118950
Purple	104919	104916	118951	118952
Black	99580	51353	123269	123271

When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.