

N **OMEGALLOY®** OMEGALLOY® is generically known as Nicrosil-Nisil.

Uncompensated

* To order, specify "MF" for connector pair, "M" for male connector only, or "F" for female connector only.

+ J, K, T, and E are ANSI designations.

U

Note: Type U (uncompensated) connectors are used with Type B thermocouples (Platinum/6% Rhodium-Platinum 30% Rhodium) Ordering Examples: OTP-U-M, uncompensated, 3-prong, heavy duty male connector. OTP-K-MF, CHROMEGA®-ALOMEGA®, 3-prong, heavy duty connector pair.

Copper

OMEGA-P®

Copper

OMEGA-N®

White

Orange

OTP-U-(*)

OTP-N-(*)