

HU363

SWITCH NOT FUSIBLE HD 600V 100A 3P NEMA1

Product availability: Stock - Normally stocked in distribution facility

Main

Commercial Status	Commercialised
Product or component type	Single Throw Safety Switch
Line Rated Current	100 A
Product certifications	UL listed
NEMA degree of protection	NEMA 1 steel
Device composition	None
Disconnecter device type	Non-fusible disconnect
Short-circuit current	200 kA maximum
Device mounting	Surface
Number of poles	3
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	14...1/0 AWG copper 12...1/0 AWG aluminium

Ordering and shipping details

Category	00008 - H&HU, 2&3P, N1, 30-200A
Discount Schedule	DE1
GTIN	00785901505846
Nbr. of units in pkg.	1
Package weight(Lbs)	16.65
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	US

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------