

Application Specific: Speed control, Ferrous / Non-ferrous, Ultrasonic



Speed control		Ferrous / Non-ferrous		Ultrasonic (Detection of any object or material)		
Type C (40 x 40)	Ø 30	Ø 18	Ø 30	M 12	M 18	M 30
15 mm	10 mm	5 mm	10 mm	51 mm	152 mm	1 m
0...12	0...8	0...4	0...8	6.4...51	25.4...152	51...991
shielded	shielded	shielded	shielded	-	-	-
P	M	M	M	P	P	P
teach mode		-	-	-	-	-
- 13...158 (- 25...70)	- 13...158 (- 25...70)	32...122 (0...50)	32...122 (0...50)	- 4...149 (- 20...65)	32...122 (0...50)	32...122 (0...50)
IP67	IP67	pre-cabled: IP68 (with connector: IP67)		IP67	IP67	IP67
40 x 40 x 15	M30 x 81	M18 x 70	M30 x 60	M12 x 50	M18 x 65	M30 x 85
48000	6000...48000 (2)	-	-	-	-	-
60...6000	6...150 / 120...3000 (2)	-	-	-	-	-
-	-	-	-	-	-	-
-	XSAV11373	-	-	-	-	-
-	XSAV12373	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
XS9C11RPBL01M12 (3)	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	-	-	-	-
-	-	-	M12 remote, L = 0.8 m	-	-	-
-	-	XS1M18KPM40D	XS1M30KPM40LD	XX512A1KAM8	XX518A1KAM12	XX630A1KAM12
10...36	10...58	10...38	10...38	10...28	10...28	10...28
200	200	200	200	100	100	100
◆ / ✱ / ▲	◆ / ✱ / -	◆ / ✱ / -	◆ / ✱ / -	◆ / ✱ / -	◆ / - / -	◆ / ✱ / -
≤ 2	≤ 2	≤ 2.6	≤ 2.6	≤ 1	≤ 1	≤ 1
-	-	1000	1000	500	500	200
-	-	-	-	-	-	-
XS9C11RMBL01U20 (4)	-	-	-	-	-	-
-	XSAV11801	-	-	-	-	-
-	XSAV12801	-	-	-	-	-
20...264	20...264	-	-	-	-	-
5...300 AC / 5...200 DC	5...350 AC / 5...200 DC	-	-	-	-	-
✱ / ▲	✱ / -	- / -	- / -	-	-	-
≤ 1.5	≤ 1.5	-	-	-	-	-
≤ 5.5	≤ 5.7	-	-	-	-	-
-	-	-	-	-	-	-

(3) Pigtail cable (L = 0.15 m) with end mounted remote control and M12 connector
 (4) Pigtail cable (L = 0.15 m) with end mounted remote control and 1/2-20UNF connector

For remote control XS9...R		Plug-in female connectors, including pre-wired versions		
 XSZBPM12	length 5 m w/o LED	 elbowed	 straight	 Snap-C
	M8	XSZCS112	XSZCS101	-
	M12	XSZCD112Y	XSZCD102Y	XSCC12FDM40V
	U20	XSZCA111Y	XSZCA101Y	-