



XUM



XUK



XUX

Design Miniature	Design Compact 50 x 50	Design Compact
1.3' / 40 cm	3.28' / 1 m	6.5' / 2 m
4" / 10cm	11.8" / 30cm	4.2' / 1.3 m
9.8" / 3 m	13' / 4 m	36" / 11 m
45.8" / 14 m	98.2" / 30 m	131" / 40 m
direct: (Mounting holes 25.5) with M3 screws	direct: (40 x 40) with M4 screws	direct: (30 / 38 / 40 / 50 / 74) with M5 screws
P / 34 x 12 x 20	P / 50 x 18 x 50	P / 91 x 30 x 70

Alignment LEDs (★): yes / Temperature range - 13...+ 131 °F (- 25...+ 55 °C) / Degree of protection (conforming to IEC 60 529): IP67 (XUK: IP65)

XUM0APSAL2	-	-
XUM0ANSAL2	-	-
-	XUK0AKSAL2	-
XUM0APSAM8 (1)	-	-
XUM0ANSAM8 (1)	-	-
-	XUK0AKSAM12	XUX0AKSAM12
-	-	XUX0AKSAT16
100 / 50	100 / 50	100 / 50
Switching frequency (Hz): 250 / Overload and short-circuit protection: YES / Output state LED (★) / Power on LED (★): yes		
XUM0AKSAL2T	XUK0AKSAL2T	XUX0AKSAM12T
XUM0AKSAM8T (1)	XUK0AKSAM12T	-
-	-	XUX0AKSAT16T
-	XUK0ARCTL2	-
-	-	XUX0ARCTT16
-	★ / ★	★ / ★
-	20	20
-	Adjustment 0 to 15 s, on delay, or off delay, or one shot	
-	XUK0ARCTL2T	-
-	-	XUX0ARCTT16T



Connector innovation


New, innovative connector that is universal, simple and fast.

For all Telemecanique brand sensors with Snap-C compatible M12 connectors (pointed pins):

- cabling to the required length without using a screwdriver or soldering iron.
- ready in just a few seconds, no stripping required.

Mounting Devices continued

Protective housing with ball joint



For	
XUM...	XUZM2004
XUK...	XUZK2004
XUX...	XUZX2004

M12 rod for ball joint



XUZ2001

Bracket for M12 rod



XUZ2003

Suitable plug-in female connectors, including pre-wired versions

Length 5 m without LED	Elbowed	Straight	Snap-C
M8	XSZCS152	XSZCS142	-
M12	XSZCD112Y	XSZCD102Y	XZCC12FDM40V

(1) M8 not Snap-C® Compatible