





1	2
CUSTOMER NAME	
CUSTOMER Part No.	1962-3

7	8	9	10
DATE	REV	DESCRIPTION	BY
2015.10.27	A/0	NEW	




P1

P2



Marking: VIDEK CAT.5E FTP PATCH 3P VERIFIED TO ANSI/TIA-568-C.2 & ISO/IEC 11801 ED.2 & EN
 <FP0819> 50288-2-2 & IEC 60332-1-2 ▲ 26AWGX4P CMX(UL) c(UL) CMH E164469-XX



orange 2	green 3
white/orange	white/green
blue 1	brown 4
white/blue	white/brown

PINOUT		
P1 (T568B)	WIRE	P2 (T568B)
1	WHT/ORG	1
2	ORG	2
3	WHT/GRN	3
6	GRN	6
4	BLU	4
5	WHT/BLU	5
7	WHT/BRN	7
8	BRN	8
S	----	S

Conductor	Bare Copper 26AWG
Insulation	Thickness:MIN at any point:0.19mm MAX AVG:0.20mm Diameter:0.86±0.06mm
Jacket	PVC Thickness:MIN at any point:0.50mm MAX AVG:0.55mm Diameter:5.6±0.2mm
Wire	CAT.5E FTP STR 26AWG*4P
Plug	YS-02 8P8C 50U"
Length	3000±50mm
Color	beige(GY825)



Key Size	△	3RD	⊕
Length	Tolerance		
(mm)	Critical	Normal	General
0-15	±0.05	±0.10	±1.0
15-60	±0.10	±0.20	
60-150	±0.15	±0.35	±1.5
150-350	±0.20	±0.50	
350-1000	±0.40	±0.65	±2.0

Part No.				
Description	CAT.5E FTP STR 26EAWG*4P YS-02			
UNIT	mm	APPROVAL	CHECKER	DRAWER
PAGE	1/1			
Draw.No.				