


S-8 SINGLE CONTACT BAYONET BASE

MINIATURE LAMP

28V 0.800A

WAMCO PART NO.		ENVELOPE SIZE		BASE TYPE	RATING		FILAMENT SHAPE	
WL-1665IF		S-8		BA15s	28V 0.800A		C-2V	
TEST VOLTS	CURRENT (A)			MIN	LIGHT OUTPUT (MSCP)		MAX	LIFE HRS
	MIN	NOM	MAX		NOM	MAX		
28V	.720	.800	.880	—	NOT RATED		—	1,000

DIMENSIONAL CHARACTERISTICS



NOTES

1. LCL = 1.13" (28.7mm)
2. Nickel-plated brass construction base
3. Frosted envelope
4. Part mark WL-1665IF
5. RoHS compliant
6. ANSI trade number 1665 IF

