

Line #	Part #	Volts	Amps	MSCP	Life	Filament
10	PL698	1.35	.060	.010	500	C6
11	PL8699	2.50	.200	.220	500	C2R
12	PL266	2.50	.350	.210	10,000	C2R
13	PL8703	2.50	.400	.550	30	C2R
14	PL8704	2.70	.060	.040	6,000	C2R
15	PL390	3.00	.015	.003	10,000	C6
16	PL7343	3.00	.030	.020	1,800	C6
17	PL7345	4.50	.120	.050	25,000	C2R
18	PL6950	5.00	.017	.018	8,000	C2R
19	PL7346	5.00	.060	.030	60,000	C2R
20	PL7347	5.00	.060	.050	25,000	C2R
21	PL3152	5.00	.060	.150	5,000	C2R
22	PL7348	5.00	.115	.150	40,000	C2R
23	PL7350	5.00	.190	.450	1,000	C2R
24	PL8705	6.00	.040	.030	10,000	C2V
25	PL8706	6.00	.200	.100	50,000	C2F
26	PL337	6.00	.200	.600	1,000	C2R
27	PL7351	6.30	.040	.020	20,000	C2V
28	PL8708	6.30	.075	.230	1,000	C2R
29	PL7352	6.30	.150	.450	3,000	C2R
30	PL379	6.30	.200	.400	20,000	C2F
31	PL398	6.30	.200	.550	5,000	C2R
32	PL709	10.00	.014	.002	50,000	C2F
33	PL397	10.00	.040	.080	5,000	C2F
34	PL7353	11.00	.022	.030	10,000	C2F
35	PL7354	12.00	.040	.120	10,000	C2F
36	PL386	14.00	.080	.300	40,000	C2F
37	PL336	14.00	.080	.500	1,500	C2F
38	PL393	14.00	.100	.500	10,000	C2F
39	PL346	18.00	.040	.150	10,000	C2F
40	PL457	22.00	.040	.300	2,000	C2F
41	PL8177	24.00	.050	.500	1,000	C2F
42	PL7355	28.00	.040	.150	10,000	C2F
43	PL388	28.00	.040	.300	7,000	C2F
44	PL334	28.00	.040	.340	4,000	C2F
45	PL334LSV	28.00	.060	.340	25,000	C2F
46	PL7356	28.00	.065	.650	5,000	C2F

T-1^{3/4} Midget Grooved

