

Life #	Part #	Volts	Amps	MSCP	Life	Filament
1	PL8798	1.25	.012	.004	1,000	C6
2	PL8910	1.35	.220	.020	25,000	C2R
3	PL7200	1.50	.010	.002	10,000	C6
4	PL7201	1.50	.015	.010	5,000	C2R
5	PL7203	1.50	.075	.030	16,000	C2R
6	PL8601	2.50	.015	.001	10,000	C2R
7	PL8732	2.50	.100	.100	10,000	C2R
8	PL8711	2.50	.320	.210	5,000	C2R
9	PL8846	3.00	.008	.001	16,000	C2R
10	PL7204	3.00	.008	.010	16,000	C2R
11	PL2128	3.00	.013	.001	16,000	C2R
12	PL7205	3.00	.015	.020	5,000	C2R
13	PL7207	3.00	.060	.030	100,000	C2R
14	PL7208	3.00	.120	.150	16,000	C2R
15	PL7209	5.00	.015	.020	10,000	C2V
16	PL8602	5.00	.017	.005	10,000	C2R
17	PL6022	5.00	.021	.034	10,000	C2R
18	PL7210	5.00	.030	.030	16,000	C2R
19	PL8729	5.00	.045	.040	10,000	C2R
20	PL680	5.00	.060	.030	60,000	C2R
21	PL683	5.00	.060	.050	25,000	C2R
22	PL6150	5.00	.060	.150	5,000	C2R
23	PL713	5.00	.075	.090	25,000	C2R
24	PL7211	5.00	.080	.150	3,000	C2R
25	PL715	5.00	.115	.150	40,000	C2R
26	PL7213	5.00	.115	.200	5,000	C2R
27	PL7216	5.00	.125	.250	5,000	C2R
28	PL8096	5.00	.145	.160	10,000	C2R
29	PL7218	10.00	.027	.100	10,000	C2F
30	PL7219	12.00	.060	.150	16,000	C2F
31	PL10569	14.00	.040	.150	16,000	C2F
32	PL8111	14.00	.065	.150	10,000	C2F
33	PL7220	18.00	.026	.150	10,000	C2F
34	PL124	24.00	.025	.130	25,000	C2F
35	PL6838	28.00	.024	.150	16,000	CC2F

T-1 Standard Wire Terminal

