

Part #	Volts	Amps	MSCP	Life	Filament
19 PL7931	1.35	.060	.010	500	C2R
20 PL7968	2.50	.200	.220	500	C2R
21 PL7868	2.50	.350	.210	10,000	C2R
22 PL7357	2.50	.400	.550	30	C2R
23 PL7838	2.70	.060	.040	6,000	C2R
24 PL7375	3.00	.015	.003	10,000	C6
25 PL7358	3.00	.030	.020	1,800	C6
26 PL7359	4.50	.120	.050	25,000	C2R
27 PL7950	5.00	.017	.018	8,000	C2R
28 PL7360	5.00	.060	.030	60,000	C2R
29 PL7361	5.00	.060	.050	25,000	C2R
30 PL3149	5.00	.060	.150	5,000	C2R
31 PL7362	5.00	.115	.150	40,000	C2R
32 PL7363	5.00	.190	.450	1,000	C2R
33 PL7945	6.00	.040	.030	10,000	C2V
34 PL7364	6.00	.200	.100	50,000	C2F
35 PL7328	6.00	.200	.600	1,000	C2R
36 PL7365	6.00	.220	.630	3,000	C2R
37 PL7380	6.30	.040	.020	20,000	C2V
38 PL7377	6.30	.075	.230	1,000	C2R
39 PL7368	6.30	.150	.450	3,000	C2R
40 PL7381	6.30	.200	.400	20,000	C2F
41 PL7349	6.30	.200	.550	5,000	C2R
42 PL7344	10.00	.014	.002	50,000	C2F
43 PL7367	10.00	.040	.080	5,000	C2F
44 PL7369	11.00	.022	.030	10,000	C2F
45 PL7371	12.00	.040	.120	10,000	C2F
46 PL7382	14.00	.080	.300	15,000	C2F
47 PL7330	14.00	.080	.500	1,500	C2F
48 PL7373	14.00	.100	.500	10,000	C2F
49 PL7370	18.00	.040	.150	10,000	C2F
50 PL7459	22.00	.040	.300	2,000	C2F
51 PL7001	24.00	.050	.500	1,000	C2F
52 PL7374	28.00	.040	.150	10,000	C2F
53 PL7387	28.00	.040	.300	7,000	C2F
54 PL7327	28.00	.040	.340	4,000	C2F
55 PL7876	28.00	.060	.340	25,000	C2F
56 PL7376	28.00	.065	.650	5,000	C2F

T-1^{3/4} Bi-Pin

