

US-159

Isolated High Retention USB 1 Port RS232

- 1 Port Isolated RS-232 USB to Serial Adapter
- Isolation: Avoid electrical damage to your expensive equipment
- High Retention USB connector with 50cm
 USB cable
- Works where many other USB to Serial devices do not
- Industrial Specification IP-50 rated -40 °C to +80 °C / -40 °F to +176 °F
- Lifetime Warranty and Support



Ultra small USB to serial adapter suitable for any environment

The US-159 has 2kV of isolation protecting from high voltage spikes, and ground potential difference. We provide our own software drivers - eliminating many common problems with USB to Serial - giving you have a reliable, stable, native com port solution.

2kV Isolation ESD protection to IEC 61000-4-2: Contact discharge: ±8 kV Air gap discharge: ±15 kV



"I have tried many off the shelf USB to Serial adapters. Some break easily, others only work some of the time. Brainboxes installed in seconds and could communicate with anything I threw at it, I would recommend this device to anyone." Colin Young, Nutek Europe

Microsoft Drivers for all popular operating systems including latest Windows Gold Partner

The high retention USB connection requires a minimum withdrawal requirement of 15N (thats a force of 1.5Kg or 3.4lbs). Connectors have orange color-coded insulator to differentiate from standard USB connectors. The connection is so strong that the port is capable of taking the weight of a bottle of champagne.



sales@brainboxes.com Tel: 0151 220 2500 Toll Free USA: +1 (888) 958 5538

US-159 - Isolated High Retention USB 1 Port RS232

Lifetime Warranty and Support:

1m cable available: US-063

Brainboxes have additional


and alternative length cables

available that are compatible

with this product

custom application.

Optional: US-063 USB Type A Plug to Type B Plug 1000mm



brai

We can help with every aspect of your project, from getting you up and running to

Packaging Information

Packaging

Packaged Weight

GTIN Universal Code

Packaged Dims

Installation CD including manual, Microsoft signed

drivers & utilities, Quick Start Guide

160x135x45 mm, 6.3x5.3x1.8 inches

0.155 kg, 5.47 ounces

837324003802