



## APC Smart-UPS Hardwire Kit for SUA 2200/3000/5000 Models

Part Number: SUA031



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

### Output

Nominal Output Voltage 120V, 208V, 230V

Maximum Total Current Draw per 30A Phase

### Input

Nominal Input Voltage 120V, 208V, 230V

Maximum Line Current per phase 30A

### Physical

Net Weight 2.00 lbs. (0.91 kg)

Maximum Height 5.00 inches (127 mm)

Maximum Width 7.00 inches (178 mm)

Maximum Depth 2.00 inches (51 mm)

Shipping Weight 3.00 lbs. (1.36 kg)

Shipping Height 5.00 inches (127 mm)

Shipping Width 7.00 inches (178 mm)

Shipping Depth 10.00 inches (254 mm)

### Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95%
<b>Conformance</b>	
Approvals	cUL Recognized, UL Recognized
Standard warranty	2 years repair or replace
<b>Sustainable Offer Status</b>	
RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab

\*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.