



APC Symmetra LX Battery Module

Part Number: SYBT5



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Output

Battery Output Voltage	120
------------------------	-----

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	1080
--------------------------------	------

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
--------------	--

Battery mounting	Enclosed battery cartridge
------------------	----------------------------

Battery manufacturer	--
----------------------	----

Expected Battery Life (years)	3 - 5
-------------------------------	-------

Battery Placement	Internal Battery
-------------------	------------------

RBC Quantity	1
--------------	---

Battery blocks per string	10
---------------------------	----

Physical

Net Weight	64.00 lbs. (29.10 kg)
------------	-----------------------

Maximum Height	5.50 inches (140 mm)
----------------	----------------------

Maximum Width	8.26 inches (210 mm)
---------------	----------------------

Maximum Depth	21.50 inches (546 mm)
---------------	-----------------------

Shipping Weight	71.00 lbs. (32.28 kg)
-----------------	-----------------------

Shipping Width	11.28 inches (286 mm)
Shipping Height	15.18 inches (385 mm)
Shipping Depth	29.52 inches (750 mm)
Units per Pallet	12.00

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 feet (0-4500 meters)

Conformance

Approvals	CSA, UL 1778
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
PEP	Available in Documentation tab
EOLI	Available in Documentation tab
Other Environmental Compliance	China RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.