Edwards® 315A-AH Heavy Duty Outdoor Motor Driven Industrial Siren



Features

- Fully enclosed motor
- Weatherproof
- Adjustable siren direction
- AC or DC operation

Description

Heavy duty, industrial design, motor driven siren that emits a continuous loud piercing wail.

Agency Approvals

UL Listed for continuous duty

Specifications

- 2.5 amp motor
- Heavy gauge aluminum construction

Installation

Mounts to any solid surface using two bolts. May be swiveled through 180°, vertically or horizontally, depending on orientation of bracket.

Applications

Used for initial installation and MRO applications in factories, lumber yards, security installations, and score boards.

Cat. No.	Volts	Amps	VA	dB at 10 Ft.
315A-AH	120V AC/DC	2.5	300	110

