

# rotronic

**Datenblatt - Fiche technique - Data sheet**


**11.04.5652**



**ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 2,0m**


**ROLINE Câble High Quality HD15 M/HD15 M  
avec noyaux de ferrite + DDC, 2,0m**

**ROLINE High Quality VGA Cable with Ferrite + DDC,  
HD15 M – HD15 M, 2 m**



Conn.1 HD15 Male Molding

Conn.2



- Electronic Test :
1. 100% Test (Open,Short, Miss Wire)
  2. Contact Resistance : 5 ohm max
  3. Insulation Resistance : 10M ohm min
  4. Hi-Pot : 300V DC/10ms

|                 |                           |                |          |
|-----------------|---------------------------|----------------|----------|
| <b>ROTRONIC</b> |                           | RoHS COMPLIANT |          |
| DESCRIPTION     | VGA Cable                 | SIZE:          | A4 mm    |
| CUSTOMER P/N    | HD15M/M W/2 FERR 2M Black | UNIT.          | mm       |
| MODEL NO.       |                           | DATE.          | 07.04.08 |
| NO.             |                           | SCALE.         | NONE     |
| HS CODE         |                           | REV.           | 1        |
| UPC             |                           | DWG NO.        |          |
| DRAW.           | LM                        |                |          |
| CHECK.          | LH                        |                |          |
| APP.            | WENTU                     |                |          |

| NO. | P/N       | DESCRIPTION  | Q'TY     | UNIT |
|-----|-----------|--|----------|------|
| 7   | R87-01001 | Ferrite Core 17.5*9.5*28.5   | 2        | pcs  |
| 6   | R87-04005 | Copper Foil 360° Solder W=3.2cm  | 12/100   | m    |
| 5   | R90-45006 | Outside Molding 45P PVC PMS:Black 3U2X   | 72/1000  | kg   |
| 4   | R91-01001 | Inside Molding PE  | 9.5/1000 | kg   |
| 3   | R86-20043 | Screw 40.5mm #4-40UNC Color:Black 3U2X   | 4        | pcs  |
| 2   | R71-15009 | HD15P Male Solder Type Insulation Blue   | 2        | pcs  |
| 1   | 61-12605  | UL2919 28AWGx3Coax+24AWGx9C+AL/MY+DW+BD Jacket Color PMS:Black 3U2X OD:8.5±0.2 | 2        | m    |
| NO. | P/N       | DESCRIPTION  | Q'TY     | UNIT |