

rotronic

Datenblatt - Fiche technique - Data sheet




ROLINE S/FTP-(PiMF-)Patchkabel Kat.6, LSOH


ROLINE Câble S/FTP Cat.6, LSOH

ROLINE S/FTP Patch Cord Cat.6, halogen-free

DATE	REV	DESCRIPTION	BY	CHKD
3/13	A/0	NEW	WZY	YZG




Marking: <LP727> roline CAT.6 SFTP 26AWGX4P TYPE LSOH IEC 332.3C -ISO/IEC 11801 & EN 50288 & TIA/EIA-568-B.2-1



orange 1 white/orange	green 2 white/green
blue 3 white/blue	brown 4 white/brown

Conductor	Bare Copper 26AWG 7/0.152±0.005mm
Insulation	Thickness:MIN at any point:0.2mm MAX AVG:0.35mm Diameter:1.05±0.05mm
Jacket	LSOH
	Thickness:MIN at any point:0.50mm MAX AVG:0.60mm Diameter:6.1±0.2mm

WIRE	CAT.6 PIMF STR 26AWG*4P
PLUG	YS-17 8P8C 50u"
Length	XXM
COLOR	GRAY852




PA/R	PINOUT		
	P1 (T568B)	WIRE	P2 (568B)
1	1	WHT/ORG	1
	2	ORG	2
2	3	WHT/GRN	3
	6	GRN	6
3	4	BLU	7
	5	WHT/BLU	8
4	7	WHT/BRN	4
	8	BRN	5

Rotronic Co., Ltd.

Unless specified on the drawing, tolerances are per the follows:

.	± 1
.X	± 0.2
.XX	± 0.05

3RD



DRAW.NO	00307	ITEM	21.15.18XX		
DEPARTMENT	R&D	DRAW	ZhaoyangWu	DATE	2009/3/13
SCALE		CHECKER		APPROVAL	
UNIT	MM	SHEET	1	OF	1

Remark#

21.15.1830	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,0.5m
21.15.1831	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,1m
21.15.1832	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,2m
21.15.1833	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,3m
21.15.1835	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,5m
21.15.1840	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,10m
21.15.1845	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,15m
21.15.1850	ROLINE S/FTP Cable Cat.6,LSOH,greyscale,20m